



Eaton® Express...
gets there Every time.

EATON

Powering Business Worldwide

E³ Express Cylinder Delivery Program

Eaton offers the world's broadest line of industrial hydraulic, pneumatic, and electro-hydraulic cylinders. And now a wide range of Eaton's Vickers® standard, tie-rod hydraulic and pneumatic cylinders are offered with 3-Day Express Delivery.

Eaton® Express...gets there Every time.

Introducing E³:

Three-Day Cylinder Delivery

Program Guidelines:

- All orders marked with 'Express Delivery' and received by 10:30 a.m., will leave Eaton's facility in just three business days.
- Eaton comprehensive standard warranty applies to all products shipped under the E³ program.
- Contact your Eaton sales team to get program terms and conditions, or with any questions.

Eaton Express Ready:

Vickers® NZ

High Pressure, Hydraulic Tie Rod

- ANSI/NFPA
- Single Rod
- 1.5"-6" Bore with Stroke Lengths to 60"
- Variety of Mount Styles Including Side Lug, Rectangular Flange Head/Cap, Rectangular Head/Cap, Clevis, and No Mount
- All Rod End Styles or Minor Modification
- Extra Rod Projection
- Standard SAE & NPTF Porting in Any Position
- Standard Cushions (Optional)
- Stop Tubes
- Normal & High Temperature Seals

Vickers® TE/TF/TL

Lower Pressure, Hydraulic/Pneumatic Tie Rod

- ANSI/NFPA
- Single Rod
- 1.5"-6" Bore with Stroke Lengths to 60"
- Variety of Mount Styles Including Side Lug, Rectangular Flange Head/Cap, Clevis, and No Mount
- All Rod End Styles or Minor Modification
- Extra Rod Projection
- Standard SAE & NPTF Porting in Any Position
- Standard Cushions (Optional)
- Standard & High Temperature Viton® Seals

Vickers® TA, TB

Medium Pressure, Hydraulic/Pneumatic Threaded

- Single Rod
- 3/4"-3" Bore with Stroke Lengths to 60"
- Variety of Mount Styles Including Side, Head Square, Clevis, Cap Square, Tapped Head, Threaded Head
- All Rod End Styles (not modified)
- Extra Rod Projection
- Standard SAE & NPTF Porting in Most Positions
- Standard Cushions (Optional)
- Standard & High Temperature Viton Seals

Vickers® VP

Aluminum, Pneumatic Tie Rod

- ANSI/NFPA
- Single Rod
- 1.5"-8" Bore with Stroke Lengths to 60"
- Variety of Mount Styles Including Side/End Lugs, Head/Cap Rectangular Flange, Head/Cap Square, Extended Tie Rod, No Mounts, and Many More
- All Rod End Styles
- Standard NPTF Porting in Any Position
- Standard Cushions (Optional)
- Standard & High Temperature Viton® Seals

NOTE: For specific coverage details, please see terms and conditions document.

Eaton
Hydraulics Group USA
14615 Lone Oak Road
Eden Prairie, MN 55344
USA
Tel: 952-937-9800
Fax: 952-294-7722
www.eaton.com/hydraulics