




Boston

Boston® Hose Wolf™ Coupling Crimp Style



HOSE DASH SIZE	FITTING PART#	CRIMP DIA.	DIE SUFFIX#	SEE FIGURE#	CRIMP MACHINE SETTING
		± .15 mm ± .006 in			
H6027					
08	Wolf-8*	29.46 mm 1.160 in	M280	4	
12	Wolf-12*	35.56 mm 1.400 in	M320**	4	
H9568					
08	Wolf-8*	30.99 mm 1.220 in	M280	4	
12	Wolf-12*	38.35 mm 1.510 in	M320**	4	
16	Wolf-16*	43.43 mm 1.710 in	M420**	4	
H9603					
16	Wolf-16*	43.43 mm 1.710 in	M420**	4	
H9682					
08	Wolf-8*	30.98 mm 1.220 in	M280	4	
12	Wolf-12*	38.35 mm 1.510 in	M320**	4	
16	Wolf-16*	43.43 mm 1.710 in	M420**	4	
H9690					
12	Wolf-12*	37.08 mm 1.460 in	M320**	4	

*Only the male pipe terminal end is qualified.

**Qualified with the FT1204, FT1307, FT1049 and ET1295 style die cages only.

Eaton

Hydraulics Operations USA
14615 Lone Oak Road
Eden Prairie, MN 55344
USA
Tel: 952-937-9800
Fax: 952-294-7722
www.hydraulics.eaton.com

Eaton

Hydraulics Operations Europe
Route de la Longeraie 7
1110 Morges
Switzerland
Tel: +41 (0) 21 811 4600
Fax: +41 (0) 21 811 4601

Eaton

Hydraulics Operations Asia Pacific
11th Floor Hong Kong New World Tower
300 Huaihai Zhong Road
Shanghai 200021
China
Tel: 86-21-6387-9988
Fax: 86-21-6335-3912



Boston