



Flow Controls



Modular Flow Regulator Valves

DGFN-06-50



CAUTION
 The valve cannot be used with pressure centered or DG-18 Air Operated Valves.

Note
 Refer to installation drawing 522650 for bolt kit information and module stacking data. The mounting bolt torque should not exceed a maximum of 700 in. lbs. (79 N.m.).

▲Included in 919646 Seal Kit


Note
 The following subplates may be used to mount a 60 series directional valve and one or more modular valves:

DGSM-06-50	(3/4 inch NPT)	Assy. No 280497
DGSM-06X-50	(1 inch NPT)	Assy. No. 280498
DGSM-06Y-50	(1-1/4 inch NPT)	Assy. No. 315213



Model Code

DGFN - 06 - 50



1 Model Series

DGFN - Directional control, gasket
mounted flow regulator module

2 Size

06 - 3/4 inch

3 Design

For satisfactory service life of these components, use full flow filtration to provide fluid which meets ISO cleanliness code 18/15 or cleaner. Selections from Eaton OFP, OFR and OFRS filter series are recommended.

Printed in U.S.A.